



# **LED Wall Mount**

## BWS150 LED200/WW PSU 220-240V 9006

LED Low Power, Power supply unit (On/Off)

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

#### **Product data**

General Information	
Lamp family code	LED-LP [LED Low Power]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	1 years
Flammability mark	For mounting on normally flammable
	surfaces
Light Technical	
Luminous Flux	240 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	41.38 lm/W
Color rendering index (CRI)	>80
Number of light sources	96
Light source color	830 warm white

Optical cover type	Polycarbonate bowl/cover UV-resistant	
Operating and Electrical		
Input Voltage	220 to 240 V	
Line Frequency	50 to 60 Hz	
Power Consumption	5.8 W	
Power Factor (Fraction)	0.4	
Connection	Screw connection block	
Cable	Cable without plug 2-pole	
Number of products on MCB of 16 A type B 1		
Temperature		
Ambient temperature range	-20 to +40 °C	
Controls and Dimming		
Dimmable	No	
Driver/power unit/transformer	Power supply unit (On/Off)	
Control interface	-	
·	·	


Datasheet, 2023, November 21 data subject to change

### **LED Wall Mount**

Constant light output	No
Mechanical and Housing	
Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and white
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall height	62 mm
Overall diameter	200 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Initial Performance (IEC Complian	it)
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BWS150 LED200/WW PSU 220-240V 9006
Full product name	BWS150 LED200/WW PSU 220-240V 9006
Full product code	911401195280
Order code	911401195280
Material Nr. (12NC)	911401195280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291995487
Numerator - Packs per outer box	24

## Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.