



# GreenPerform Troffer

## RC100B LED27S 865 W60L60 PSU G3

GreenPerform Troffer, 117 lm/W, 865 cool daylight

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 600 °C, duration 30 s
Light Technical	
Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	117 lm/W
Color rendering index (CRI)	80
Light source color	865 cool daylight
Optical cover type	Variable linear-lens array in polycarbonate cover

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	3 A
Inrush time	62 ms
Power Consumption	23 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 24	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Metal
Optic material	Polycarbonate

## GreenPerform Troffer

Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	597 mm
Overall width	597 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 597 x 597 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

### Application Conditions

Suitable for random switching	No
-------------------------------	----

### Product Data

Order product name	RC100B LED27S 865 W60L60 PSU G3
Full product name	RC100B LED27S 865 W60L60 PSU G3
Full product code	911401508651
Order code	01508651
Material Nr. (12NC)	911401508651
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

