# **PHILIPS** Lighting



# **Downlight DN060B**

## DN060B LED18S/830 PSU WH

Downlight DN060B, 18 W, 1800 lm, 3000 K, Opal

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

#### **Product data**

General Information	
Light source replaceable	No
Gear	-
Lighting Technology	LED
Warranty period	3 years
Value ladder	Value
Light Technical	
Luminous Flux	1,800 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>80
Light source color	830 warm white
Luminaire light beam spread	110°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	18 W
Power Factor (Fraction)	0.9

Connection	Push-in connector 2-pole
Temperature	
Ambient temperature range	0 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Material	Plastic
Reflector material	Steel
Optic material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Opal
Overall length	225 mm
Overall width	225 mm
Overall height	120 mm
Overall diameter	233 mm

### Downlight DN060B

Dimensions (Height x Width x Depth)	120 x 225 x 225 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance at median useful life* 50000 h	L65

25 ℃
DN060B LED18S/830 PSU WH
DN060B LED18S/830 PSU WH
871016330661299
911401531931
911401531931
1
8710163306612
8
8710163306896

#### Dimensional drawing



#### Photometric data



Light Distribution Diagram - DN060B LED18S/830 PSU WH

- 749-10	USI dayar	1.75
		100.000
		-
121	1.1	-
	1 +	
~	Langer Table	
Consultation and the	1 1111	1111
		3338

General uniform lighting - DN060B LED18S/830 PSU WH

Downlight DN060B



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, November 24 - data subject to change