



GreenSpace Downlight G4

DN291B 1xDLED-4000 PSU WH

GreenSpace Downlight G4, 11.6 W, 1000 lm, 4000 K, Beam angle 60 to 120°, Matte, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information		Luminaire light beam spread	
Light source replaceable	No		90°
Number of gear units	1 unit	Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
CE mark	CE mark	Line Frequency	50 or 60 Hz
ENEC mark	-	Power Consumption	11.6 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.9
		Number of products on MCB of 16 A type B	30
Light Technical		Temperature	
Luminous Flux	1,000 lm	Ambient temperature range	-20 to +40 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	89 lm/W	Dimmable	No
Color rendering index (CRI)	>80	Driver/power unit/transformer	Power supply unit (On/Off)
Number of light sources	1	Control interface	-
Light source color	840 neutral white		
Optic type	Beam angle 60 to 120°		
Optical cover type	Transparent bowl with white cover		



GreenSpace Downlight G4

Constant light output	Yes
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Matte
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	DN291B 1xDLED-4000 PSU WH
Full product name	DN291B 1xDLED-4000 PSU WH
Full product code	911401565021
Order code	911401565021
Material Nr. (12NC)	911401565021
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218

