



GreenSpace G5

DN390B LED6/840 PSU D100 WH GM

GreenSpace G5, 5.5 W, 600 lm, 4000 K, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	109 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	72 degree(s)
Light source color	840 neutral white
Optic type	High-gloss high reflectance
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	80°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	2.2 A
Inrush time	0.045 ms
Power Consumption	5.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Number of products on MCB of 16 A type B 48	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

GreenSpace G5

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	98 mm
Overall diameter	120 mm
Dimensions (Height x Width x Depth)	98 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38) SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.12 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	DN390B LED6/840 PSU D100 WH GM
Full product name	DN390B LED6/840 PSU D100 WH GM
Full product code	872016972029900
Order code	911401577841
Material Nr. (12NC)	911401577841
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169720299
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169720299

Dimensional drawing

