



GreenSpace G5

DN393B LED22/865 PSU D200 ALU GM

GreenSpace G5, 19 W, 2200 lm, 6500 K, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	2,200 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	60 degree(s)
Light source color	865 cool daylight
Optic type	High-gloss high reflectance
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	65°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	2.2 A
Inrush time	0.045 ms
Power Consumption	19 W
Power Factor (Fraction)	0.95
Connection	Push-in connector 6-pole
Number of products on MCB of 16 A type B 48	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No

GreenSpace G5

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	108 mm
Overall diameter	216 mm
Dimensions (Height x Width x Depth)	108 x 0 x 0 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31,0.32) SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.12 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	DN393B LED22/865 PSU D200 ALU GM
Full product name	DN393B LED22/865 PSU D200 ALU GM
Full product code	872016972025100
Order code	911401580641
Material Nr. (12NC)	911401580641
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169720251
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169720251

Dimensional drawing

