



Tango G3 – BVP38x

BVP383 LED408/NW 310W 220–240V AWB ANZ

Tango G3 – BVP38x, 40800 lm, 310 W, 740 neutral white, Safety class I

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information		Power Consumption	
Driver included	Yes		310 W
Lighting Technology	LED	Power Factor (Fraction)	0.9
CE mark	CE mark	Connection	Flying leads/wires
Light Technical		Cable	Cable 0.5 m without plug
Luminous Flux	40,800 lm	Temperature	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	–40 to +50 °C
Luminous Efficacy (rated) (Nom)	134 lm/W	Controls and Dimming	
Color rendering index (CRI)	>70	Dimmable	No
Light source color	740 neutral white	Control interface	–
Optical cover type	Polycarbonate micro lens optic	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminum die cast
Input Voltage	220 to 240 V	Optical cover material	Polycarbonate
Line Frequency	50 or 60 Hz		

Tango G3 - BVP38x

Housing Color	Aluminum and gray
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BVP383 LED408/NW 310W 220-240V AWB ANZ
Full product name	BVP383 LED408/NW 310W 220-240V AWB ANZ
Full product code	911401604606
Order code	911401604606
Material Nr. (12NC)	911401604606
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

