



Tango G3 - BVP38x

BVP384 LED614/NW 490W 220-240V SMB GM

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognised safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data


General Information		Optical cover/lens material	
Lamp colour code	740 neutral white	Optical cover/lens material	Polycarbonate
Driver included	Yes	Colour	Aluminium and Grey
Optical cover/lens type	PC-MLO [Polycarbonate micro lens optic]	Approval and Application	
Control interface	-	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Connection	Flying leads/wires	Mech. impact protection code	IK08 [5 J vandal-protected]
Cable	Cable 0.5 m without plug	Initial Performance (IEC Compliant)	
Protection class IEC	Safety class I (I)	Initial luminous flux	61400 lm
CE mark	CE mark	Luminous flux tolerance	+/-10%
Operating and Electrical		Initial LED luminaire efficacy	127 lm/W
Input voltage	220 to 240 V	Lamp colour temperature	4000 K
Input frequency	50 or 60 Hz	Colour Rendering Index	>70
Power factor (min.)	0.9	Initial input power	490 W
Controls and Dimming		Power consumption tolerance	+/-10%
Dimmable	No	Application Conditions	
Mechanical and Housing		Ambient temperature range	-40 to +50 °C
Housing material	Aluminum die-cast		

Tango G3 - BVP38x


Product Data

Full product code	911401617106
Order product name	BVP384 LED614/NW 490W 220-240V SMB GM
Order code	911401617106
Local Code	0
Numerator – quantity per pack	1

Numerator – packs per outer box	1
Material no. (12NC)	911401617106
Net weight (piece)	18.999 kg



Dimensional drawing



BVP38x Tango G3

