



UNIstrip G3

BCP280 G3 20LEDHP/4000 L1200 24V A DMX

UNIstrip G3, 4000 lm, 40 W, Neutral white, Dynamix DMX, Safety class III, Mounting bracket adjustable

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNIstrip G3 offers reliable quality and outstanding performance.

Product data

General Information		
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	No	
Light source engine type	LED	
Lighting Technology	LED	
CE mark	CE mark	
Warranty period	3 years	
Flammability mark	For mounting on normally flammable surfaces	
EU RoHS compliant	Yes	
Light Technical		
Luminous Flux	4,000 lm	
Standard tilt angle posttop	-	
Standard tilt angle side entry	-	
Correlated Color Temperature (Nom)	4000 K	
Luminous Efficacy (rated) (Nom)	100 lm/W	

80

Neutral white

Acrylic bowl/cover clear

Operating and Electrical	
Input Voltage	24 DC V
Inrush current	30 A
Inrush time	0.03 ms
Power Consumption	40 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.0 m without plug
Temperature	
Ambient temperature range	-40 to +50 ℃
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Electronic transformer
Control interface	Dynamix DMX
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Acrylate

Color rendering index (CRI)

Light source color

Optical cover type

UNIstrip G3

Optical cover material	Acrylate
Housing Color	Aluminum and black
Mounting device	Mounting bracket adjustable
Optical cover shape	Conical
Optical cover finish	Clear
Overall length	1,198 mm
Overall width	50 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 50 x 1198 mm

IK06 [1 J]

Safety class III

IP66 [Dust penetration-protected, jet-proof]


Power consumption tolerance	+/-10%	
Application Conditions		
Maximum dim level	0% (digital)	
Product Data		
Order product name	BCP280 G3 20LEDHP/4000 L1200 24V A DMX	
Full product name	BCP280 G3 20LEDHP/4000 L1200 24V A DMX	
Full product code	911401623304	
Order code	911401623304	
Material Nr. (12NC)	911401623304	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	8	

Mech. impact protection code Protection class IEC

Approval and Application Ingress protection code

Initial Performance (IEC Compliant)				
Luminous flux tolerance	+/-10%			

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change