



UNIstrip G3

BCP280 G3 5LEDHP/3000 L300 24V W

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNIstrip G3 offers reliable quality and outstanding performance.

Product data

General Information	
Light source colour	Warm white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	ET [Electronic transformer]
Driver included	No
Optical cover/lens type	ACC [Acrylic bowl/cover clear]
Control interface	-
Connection	Flying leads/wires
Cable	Cable 1.0 m without plug (C1K)
Protection class IEC	Safety class III (III)
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
Warranty period	3 years
Outdoor optic type	Wide beam angle 45°
Constant light output	No
LED engine type	LED
Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input voltage	24 DC V
Inrush current	30 A

Inrush time	0.03 ms
Power factor (min.)	0.95
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing material	Aluminum extruded
Optic material	Acrylate
Optical cover/lens material	Acrylate
Mounting device	MBA [Mounting bracket adjustable]
Optical cover/lens shape	Conical
Optical cover/lens finish	Clear
Overall length	335 mm
Overall width	50 mm
Overall height	65 mm
Colour	Aluminum and black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Initial Performance (IEC Compliant)	
Initial luminous flux	890 lm
Luminous flux tolerance	+/-10%

UNiStrip G3

Initial LED luminaire efficacy	93 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	80
Initial input power	9.6 W
Power consumption tolerance	+/-10%


Application Conditions

Ambient temperature range	-40 to +50 °C
Maximum dimming level	Not applicable


Product Data

Full product code	911401623704
-------------------	--------------

Order product name	BCP280 G3 5LEDHP/3000 L300 24V W
Order code	01623704
Numerator – quantity per pack	1
Numerator – packs per outer box	8
Material no. (12NC)	911401623704
Net weight (piece)	0.549 kg



Dimensional drawing



BCP280/383/384/385 UNiStrip G3

