



UNistrip G3

BCP280 G3 20LEDHP/3000 L1200 24V A

UNistrip G3, 3560 lm, 40 W, Warm white, Safety class III,
Mounting bracket adjustable

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNistrip G3 offers reliable quality and outstanding performance.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	3,560 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	80
Light source color	Warm white
Optical cover type	Acrylic bowl/cover clear

Operating and Electrical	
Input Voltage	24 DC V
Inrush current	30 A
Inrush time	0.03 ms
Power Consumption	40 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.0 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Acrylate

UNIstrip G3

Optical cover material	Acrylate
Housing Color	Aluminum and black
Mounting device	Mounting bracket adjustable
Optical cover shape	Conical
Optical cover finish	Clear
Overall length	1,198 mm
Overall width	50 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 50 x 1198 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BCP280 G3 20LEDHP/3000 L1200 24V A
Full product name	BCP280 G3 20LEDHP/3000 L1200 24V A
Full product code	911401624104
Order code	01624104
Material Nr. (12NC)	911401624104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

