



SmartBright LED Floodlight

BVP176 LED190/WW 200W WB GREY CE

SmartBright LED Floodlight, 19000 lm, 200 W, 730 warm white, 30° x 80°, Safety class I, Mounting bracket adjustable

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards, offering you reliable and long-lasting performance.

Product data

General Information		Optical cover type	
Lamp family code	LED190 [LED module 19000 lm]	Luminaire light beam spread	Polycarbonate bowl/cover UV-resistant
Light source replaceable	No		30° x 80°
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Inrush current	11.5 A
Flammability mark	For mounting on normally flammable surfaces	Inrush time	0.077 ms
ENEC mark	-	Power Consumption	200 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	19,000 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	3000 K	Cable	Cable 0.6 m without plug
Luminous Efficacy (rated) (Nom)	95 lm/W	Number of products on MCB of 16 A type B	13
Color rendering index (CRI)	>70	Temperature	
Light source color	730 warm white	Ambient temperature range	-40 to +45 °C

SmartBright LED Floodlight

Controls and Dimming

Dimmable	No
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	390 mm
Overall width	287 mm
Overall height	62 mm
Effective projected area	0.1365 m ²
Dimensions (Height x Width x Depth)	62 x 287 x 390 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP176 LED190/WW 200W WB GREY CE
Full product name	BVP176 LED190/WW 200W WB GREY CE
Full product code	871016331966799
Order code	911401629704
Material Nr. (12NC)	911401629704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163319667
Numerator - Packs per outer box	3
EAN/UPC - Case	8710163319759

Dimensional drawing

