



RoadFlair Gen2

BRP492 LED215/NW 150W 220-240V DM P7 GM

RoadFlair Gen2, 21500 lm, 150 W, 740 neutral white, Analog, Safety class I

RoadFlair Gen2 is brand new design road lighting product family, set to meet customers' all-round requirements, including high lumen efficacy for energy saving and sustainability, aesthetic design for nice shape and appearance, quality material and components for product reliability and long lifetime, professional optics for various applications fulfillment, dimming and system control interface for improving municipal operations and offering future-proof features. RoadFlair Gen2 competitive price would help on the acceleration of road lighting LED transformation, to a more sustainable society and smarter city.

Product data

General Information		Power Consumption	
Driver included	Yes	Power Factor (Fraction)	0.95
CE mark	CE mark	Connection	Screw connection block 3-pole
Light Technical		Cable	-
Luminous Flux	21,500 lm	Temperature	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	-40 to +50 °C
Luminous Efficacy (rated) (Nom)	140 lm/W	Controls and Dimming	
Color rendering index (CRI)	>70	Dimmable	Yes
Light source color	740 neutral white	Control interface	Analog
Optical cover type	Polycarbonate micro lens optic	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminium pressure die cast
Input Voltage	220 to 240 V	Optical cover material	Polycarbonate
Line Frequency	50 or 60 Hz		

RoadFlair Gen2

Housing Color	Aluminum and gray
Overall length	404 mm
Overall width	230 mm
Overall height	182 mm
Dimensions (Height x Width x Depth)	182 x 230 x 404 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BRP492 LED215/NW 150W 220-240V DM P7 GM
Full product name	BRP492 LED215/NW 150W 220-240V DM P7 GM
Full product code	872016972822600
Order code	911401673906
Material Nr. (12NC)	911401673906
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169728226
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169728226

Dimensional drawing

