



SmartBright LED Floodlight

BVP174 LED95/CW 100W WB GREY CE

SmartBright LED Floodlight, 9500 lm, 100 W, 757 cool white, 30° x 80°, Safety class I, Mounting bracket adjustable

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards, offering you reliable and long-lasting performance.

Product data

General Information		Luminaire light beam spread	
Lamp family code	LED66 [LED module 6600 lm]	30° x 80°	
Light source replaceable	No	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	9.7 A
CE mark	CE mark	Inrush time	0.065 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	100 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	9,500 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	5700 K	Cable	Cable 0.6 m without plug
Luminous Efficacy (rated) (Nom)	95 lm/W	Number of products on MCB of 16 A type B 26	
Color rendering index (CRI)	>70	Temperature	
Light source color	757 cool white	Ambient temperature range	-40 to +45 °C
Optical cover type	Polycarbonate bowl/cover UV-resistant		

SmartBright LED Floodlight

Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	356 mm
Overall width	190 mm
Overall height	53 mm
Effective projected area	0.11036 m²
Dimensions (Height x Width x Depth)	53 x 190 x 356 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP174 LED95/CW 100W WB GREY CE
Full product name	BVP174 LED95/CW 100W WB GREY CE
Full product code	871016332101199
Order code	911401689704
Material Nr. (12NC)	911401689704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163321011
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163321615

Dimensional drawing

