

SmartBright LED Floodlight

BVP173 LED66/CW 70W WB GREY SAA KC

SmartBright LED Floodlight, 6650 lm, 70 W, 757 cool white, 30° x 80°, Safety class I, Mounting bracket adjustable

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards,offering you reliable and long-lasting performance.

Product data

General Information	
Lamp family code	LED66 [LED module 6600 lm]
Light source replaceable	No
Driver included	Yes
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces

Light Technical	
Luminous Flux	6,650 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color rendering index (CRI)	>70
Light source color	757 cool white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	30° x 80°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	9.2 A
Inrush time	0.066 ms
Power Consumption	70 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.6 m without plug
Number of products on MCB of 16 A type B	37

Temperature	
Ambient temperature range	-40 to +45 °C

SmartBright LED Floodlight

Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	300 mm
Overall width	190 mm
Overall height	40 mm
Effective projected area	0.0795 m²
Dimensions (Height x Width x Depth)	40 x 190 x 300 mm


Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	BVP173 LED66/CW 70W WB GREY SAA KC
Full product name	BVP173 LED66/CW 70W WB GREY SAA KC
Full product code	871016332092299
Order code	911401690404
Material Nr. (12NC)	911401690404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163320922
Numerator - Packs per outer box	8
EAN/UPC - Case	8710163321523

Dimensional drawing



*Configuration for Australia, New Zealand and Korea

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.