

Greenspace Flex

RS378Z M55 D78 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information	
Light source engine type	-
Accessory color	White
CE mark	-
Warranty period	3 years
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 600 °C, duration 30 s

Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Beam angle of light source	- degree(s)
Light source color	-
Optic type	-
Optical cover type	-

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-

Temperature	
Ambient temperature range	-20 to +45 °C

Controls and Dimming	
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	42 mm
Overall diameter	85 mm
Dimensions (Height x Width x Depth)	42 x 0 x 0 mm

Greenspace Flex

Material	Aluminum


Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Protection class IEC	-


Application Conditions	
Maximum dim level	Not applicable


Product Data	
Order product name	RS378Z M55 D78 R-R FX D


Full product name	RS378Z M55 D78 R-R FX D
Full product code	692382865958599
Order code	911401721712
Material Nr. (12NC)	911401721712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659585
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659622

Dimensional drawing









Cut out: Ø78

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.