



# GreenSpace Flex

## RS378Z M55 D78 S-S AJ D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer’s requirement.

### Product data

General Information	
Light source engine type	-
Accessory color	White
CE mark	-
Warranty period	3 years
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 600 °C, duration 30 s
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Beam angle of light source	- degree(s)
Light source color	-
Optic type	-
Optical cover type	-
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-

Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	85 mm
Overall width	85 mm
Overall height	52 mm
Overall diameter	0 mm
Dimensions (Height x Width x Depth)	52 x 85 x 85 mm

Greenspace Flex

Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Protection class IEC	-
Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	RS378Z M55 D78 S-S AJ D
Full product name	RS378Z M55 D78 S-S AJ D
Full product code	911401721722
Order code	911401721722
Material Nr. (12NC)	911401721722
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing

