



# Greenspace Flex

RS378Z M55 D75 R-R AJ

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

## Product data



General Information		Controls and Dimming	
Light source engine type	-	Control interface	-
Accessory color	White	Constant light output	No
CE mark	-		
Warranty period	3 years	Mechanical and Housing	
		Housing Material	Aluminum
Light Technical		Optical cover material	-
Correlated Color Temperature (Nom)	-	Fixation material	Aluminum
Color rendering index (CRI)	-	Housing Color	White
Light source color	-	Optical cover finish	-
Optical cover type	-	Overall length	0 mm
		Overall width	0 mm
Operating and Electrical		Overall height	17 mm
Input Voltage	- V	Overall diameter	85 mm
Line Frequency	- Hz	Dimensions (Height x Width x Depth)	17 x 0 x 0 mm
Cable	-	Material	Aluminum
Number of products on MCB of 16 A type B	-	Approval and Application	
		Ingress protection code	IP20 [Finger-protected]
Temperature		Mech. impact protection code	IK04 [0.5 J standard plus]
Ambient temperature range	-20 to +45 °C		

# Greenspace Flex

Protection class IEC	-
<b>Application Conditions</b>	
Maximum dim level	Not applicable
<b>Product Data</b>	
Order product name	RS378Z M55 D75 R-R AJ
Full product name	RS378Z M55 D75 R-R AJ

Full product code	911401721792
Order code	911401721792
Material Nr. (12NC)	911401721792
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

## Dimensional drawing



Cut out: Ø75

