



Greenspace Flex

RS378Z M55 D75 R-R FX PH WP

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.



Product data

General Information		Controls and Dimming	
Light source engine type	-	Control interface	-
Accessory color	White	Constant light output	No
CE mark	-		
Warranty period	3 years		
Light Technical		Mechanical and Housing	
Correlated Color Temperature (Nom)	-	Housing Material	Aluminum
Color rendering index (CRI)	-	Optical cover material	-
Light source color	-	Fixation material	Aluminum
Optical cover type	-	Housing Color	White
		Optical cover finish	-
		Overall length	0 mm
		Overall width	0 mm
		Overall height	48 mm
		Overall diameter	88 mm
		Dimensions (Height x Width x Depth)	48 x 0 x 0 mm
		Material	Aluminum
Operating and Electrical		Approval and Application	
Input Voltage	- V	Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Line Frequency	- Hz	Mech. impact protection code	IK04 [0.5 J standard plus]
Cable	-		
Number of products on MCB of 16 A type B	-		
Temperature			
Ambient temperature range	-20 to +45 °C		

Protection class IEC	-
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	RS378Z M55 D75 R-R FX PH WP
Full product name	RS378Z M55 D75 R-R FX PH WP
Full product code	692382865957899

Order code	911401721852
Material Nr. (12NC)	911401721852
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828659578
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828659615

Dimensional drawing



Cut out: Ø75

