



GreenSpace Flex

RS378Z M55 D75 R-R AJ PH

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

General Information	
Light source engine type	-
Accessory color	White
CE mark	-
Warranty period	3 years
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Light source color	-
Optical cover type	-
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	-20 to +45 °C

Controls and Dimming	
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	48 mm
Overall diameter	88 mm
Dimensions (Height x Width x Depth)	48 x 0 x 0 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]

Protection class IEC	-
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	RS378Z M55 D75 R-R AJ PH
Full product name	RS378Z M55 D75 R-R AJ PH
Full product code	872016953213799

Order code	911401721872
Material Nr. (12NC)	911401721872
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532137
Numerator - Packs per outer box	48
EAN/UPC - Case	8720169543621

Dimensional drawing

