



Greenspace Flex

RS378Z M70 D90 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer’s requirement.

Product data

General Information	
Light source engine type	-
Accessory color	White
CE mark	-
Warranty period	3 years
Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	-
Light source color	-
Optical cover type	-
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Cable	-
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	-20 to +45 °C



Controls and Dimming	
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	-
Fixation material	Aluminum
Housing Color	White
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	55 mm
Overall diameter	102 mm
Dimensions (Height x Width x Depth)	55 x 0 x 0 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]

Greenspace Flex

Protection class IEC	-
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	RS378Z M70 D90 R-R FX D
Full product name	RS378Z M70 D90 R-R FX D
Full product code	872016953216899

Order code	911401722012
Material Nr. (12NC)	911401722012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532168
Numerator - Packs per outer box	36
EAN/UPC - Case	8720169543652

Dimensional drawing



Cut out: Ø90

