

SmartBright Slim Panel G2

RC091V LED26S/840 PSU W60L60 GM G2

Economic office lighting solution

Product data

General Information	
Lamp colour code	840 neutral white
Optical cover/lens type	Polystyrene bowl/cover prismatic
Control interface	-
Protection class IEC	Safety class II (II)
CE mark	CE mark
Number of products on MCB	74
LED engine type	LED

Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 or 60 Hz
Power factor (min.)	0.9

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Aluminum extruded
Optical cover/lens material	Polystyrene
Optical cover/lens finish	Frosted
Colour	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]


Initial Performance (IEC Compliant)	
Initial luminous flux	2600 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	90 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial input power	29 W
Power consumption tolerance	+/-10%

Application Conditions	
Ambient temperature range	-10 to +35 °C


Product Data	
Full product code	871016332467800
Order product name	RC091V LED26S/840 PSU W60L60 GM G2
EAN/UPC – product	8710163324678
Order code	32467800
Numerator – quantity per pack	1
Numerator – packs per outer box	4

SmartBright Slim Panel G2

Material no. (12NC)	911401723772
Net weight (piece)	2.000 kg



Dimensional drawing



RC091V LED26S/LED36S PSU

