PHILIPS Lighting



LED Wall Mount

BWS151 LED200/NW PSU 220-240V 9006

LED Wall Mount, 250 lm, 5.8 W, 740 neutral white, Safety class II, Allen screw fixation

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

Product data

General Information	
Lamp family code	LED-LP [LED Low Power]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	1 years
Flammability mark	For mounting on normally flammable
	surfaces
Light Technical	
Luminous Flux	250 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	43.10 lm/W
Color rendering index (CRI)	>70
Number of light sources	96

Light source color	740 neutral white	
Optical cover type	Polycarbonate bowl/cover UV-resistant	
Operating and Electrical		
Input Voltage	220 to 240 V	
Line Frequency	50 to 60 Hz	
Power Consumption	5.8 W	
Power Factor (Fraction)	0.4	
Connection	Screw connection block	
Cable	Cable without plug 2-pole	
Number of products on MCB of 16 A type B 1		
Temperature		
Ambient temperature range	-20 to +40 °C	
Controls and Dimming		
Dimmable	No	

LED Wall Mount

Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and white
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall length	200 mm
Overall width	200 mm
Overall height	62 mm
Dimensions (Height x Width x Depth)	62 x 200 x 200 mm

IP65 [Dust penetration-protected, jet-proof]


IK08 [5 J vandal-protected]

Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BWS151 LED200/NW PSU 220-240V 9006
Full product name	BWS151 LED200/NW PSU 220-240V 9006
Full product code	872016953230499
Order code	53230499
Material Nr. (12NC)	911401724201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532304
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169543799

Dimensional drawing

Approval and Application Ingress protection code

Mech. impact protection code







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, May 1 - data subject to change