



LED Wall Mount

BWS151 LED200/WW PSU 220-240V 7043

LED Wall Mount, 240 lm, 5.8 W, 830 warm white, Safety class II, Allen screw fixation

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

Product data

General Information		Light source color	
Lamp family code	LED-LP [LED Low Power]	830 warm white	
Light source replaceable	No	Optical cover type	
Number of gear units	1 unit	Polycarbonate bowl/cover UV-resistant	
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	
CE mark	CE mark	220 to 240 V	
Warranty period	1 years	Line Frequency	
Flammability mark	For mounting on normally flammable surfaces	50 to 60 Hz	
		Power Consumption	
		5.8 W	
		Power Factor (Fraction)	
		0.4	
		Connection	
		Screw connection block	
		Cable	
		Cable without plug 2-pole	
		Number of products on MCB of 16 A type B 1	
Light Technical		Temperature	
Luminous Flux	240 lm	Ambient temperature range	
Correlated Color Temperature (Nom)	3000 K	-20 to +40 °C	
Luminous Efficacy (rated) (Nom)	41.38 lm/W		
Color rendering index (CRI)	>80	Controls and Dimming	
Number of light sources	96	Dimmable	
		No	

LED Wall Mount

Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Dark gray
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall length	200 mm
Overall width	200 mm
Overall height	62 mm
Dimensions (Height x Width x Depth)	62 x 200 x 200 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class II
----------------------	-----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BWS151 LED200/WW PSU 220-240V 7043
Full product name	BWS151 LED200/WW PSU 220-240V 7043
Full product code	872016953231199
Order code	911401724301
Material Nr. (12NC)	911401724301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532311
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169543805

Dimensional drawing

