



UNIUrban

BGP461 LED40 WW 110-277V TA

UNIUrban, 4000 lm, 33 W, Warm white, Safety class I, Side-entry for diameter 60 mm

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Product data

General Information		Power Consumption	
Light source replaceable	No		33 W
Driver included	Yes	Power Factor (Fraction)	0.95
Light source engine type	LED	Connection	Flying leads/wires
Value ladder	Performance	Cable	Cable 0.2 m without plug
CE mark	CE mark	Temperature	
Flammability mark	-	Ambient temperature range	-40 to +50 °C
Light Technical		Controls and Dimming	
Luminous Flux	4,000 lm	Dimmable	No
Standard tilt angle posttop	15°	Control interface	-
Correlated Color Temperature (Nom)	3000 K	Constant light output	No
Luminous Efficacy (rated) (Nom)	120 lm/W	Mechanical and Housing	
Color rendering index (CRI)	≥70	Housing Material	Aluminum
Light source color	Warm white	Optical cover material	Tempered glass
Optical cover type	Polycarbonate micro lens optic	Housing Color	Grey
Operating and Electrical		Mounting device	Side-entry for diameter 60 mm
Input Voltage	110 to 277 V	Optical cover finish	Clear
Line Frequency	50 to 60 Hz	Overall length	691 mm

Overall width	480 mm
Overall height	66 mm
Overall diameter	488 mm
Dimensions (Height x Width x Depth)	66 x 480 x 691 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	BGP461 LED40 WW 110-277V TA
Full product name	BGP461 LED40 WW 110-277V TA
Full product code	911401727522
Order code	911401727522
Material Nr. (12NC)	911401727522
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

