



UNIUrban

BSS461 LED120 NW 110-277V CLASSIC

UNIUrban, 12000 lm, 100 W, Neutral white, Safety class I,
Catenary pole 35mm with Ø 10mm hole

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

Product data

General Information	
Light source replaceable	No
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
CE mark	CE mark
Flammability mark	-
Light Technical	
Luminous Flux	12,000 lm
Standard tilt angle posttop	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥70
Light source color	Neutral white
Optical cover type	Polycarbonate micro lens optic
Operating and Electrical	
Input Voltage	110 to 277 V
Line Frequency	50 to 60 Hz

Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.6 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Optical cover material	Tempered glass
Housing Color	Grey
Mounting device	Catenary pole 35mm with Ø 10mm hole
Optical cover finish	Clear
Overall height	371 mm

Overall diameter	482 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BSS461 LED120 NW 110-277V CLASSIC
Full product name	BSS461 LED120 NW 110-277V CLASSIC
Full product code	911401727792
Order code	911401727792
Material Nr. (12NC)	911401727792
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

