



# Essential SmartBright G3 LED Floodlight

## BVP150 LED25/CW 220-240V 30W SWB CQC

Essential SmartBright G3 LED Floodlight, 2550 lm, 30 W, 865 cool daylight, Symmetrical wide beam, 110°, Safety class I, Mounting bracket adjustable

The Essential SmartBright G3 LED floodlight comes with a compact and sturdy design. Its light weight with robust die-cast aluminum housing and corrosion-proof coating, suitable for general outdoor application. Higher efficacy than last generation, achieves more energy savings.

### Product data

General Information			
Light source replaceable	No	Color rendering index (CRI)	>80
Driver included	Yes	Light source color	865 cool daylight
Light source engine type	LED	Optical cover type	Glass bowl/cover
Lighting Technology	LED	Luminaire light beam spread	110°
CE mark	CE mark	Optic type outdoor	Symmetrical wide beam
Flammability mark	For mounting on normally flammable surfaces	Operating and Electrical	
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	2,550 lm	Line Frequency	50 to 60 Hz
Standard tilt angle posttop	-	Inrush current	1 A
Standard tilt angle side entry	-	Inrush time	0.0111 ms
Correlated Color Temperature (Nom)	6500 K	Power Consumption	30 W
Luminous Efficacy (rated) (Nom)	85 lm/W	Power Factor (Fraction)	0.9
		Connection	Flying leads/wires
		Cable	Cable 0.3 m without plug

Essential SmartBright G3 LED Floodlight

Number of products on MCB of 16 A type B 71	
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Glass
Fixation material	Steel
Housing Color	Black
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	170 mm
Overall width	130 mm
Overall height	29 mm
Dimensions (Height x Width x Depth)	29 x 130 x 170 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK06 [1 J]
Surge Protection (Common/Differential)	Surge protection level until 2 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP150 LED25/CW 220-240V 30W SWB CQC
Full product name	BVP150 LED25/CW 220-240V 30W SWB CQC
Full product code	692382863088199
Order code	911401732692
Material Nr. (12NC)	911401732692
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828630881
Numerator - Packs per outer box	16
EAN/UPC - Case	6923828631178

Dimensional drawing

