



Essential SmartBright G3 LED Floodlight

BVP150 LED8/NW 220-240V 10W SWB SAA

Essential SmartBright G3 LED Floodlight, 850 lm, 10 W, 840 neutral white, Symmetrical wide beam, Safety class I, Mounting bracket adjustable

The Essential SmartBright G3 LED floodlight comes with a compact and sturdy design. Its light weight with robust die-cast aluminum housing and corrosion-proof coating, suitable for general outdoor application. Higher efficacy than last generation, achieves more energy savings.

Product data

General Information		Optical cover type	Glass bowl/cover
Light source replaceable	No	Optic type outdoor	Symmetrical wide beam
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Power Consumption	10 W
Flammability mark	For mounting on normally flammable surfaces	Power Factor (Fraction)	0.9
Light Technical		Connection	Flying leads/wires
Luminous Flux	850 lm	Cable	Cable 0.3 m without plug
Standard tilt angle posttop	-	Temperature	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	-40 to +50 °C
Luminous Efficacy (rated) (Nom)	85 lm/W		
Color rendering index (CRI)	>80		
Light source color	840 neutral white		

Essential SmartBright G3 LED Floodlight

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Glass
Fixation material	Steel
Housing Color	Black
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	115 mm
Overall width	92 mm
Overall height	28 mm
Dimensions (Height x Width x Depth)	28 x 92 x 115 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Surge Protection (Common/Differential)	Surge protection level until 2 kV

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP150 LED8/NW 220-240V 10W SWB SAA
Full product name	BVP150 LED8/NW 220-240V 10W SWB SAA
Full product code	871016333604699
Local code description	BVP150L8NW10W
Order code	911401736512
Material Nr. (12NC)	911401736512
Local order code	BVP150L8NW10W
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163336046
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163336503

Dimensional drawing

