



UniStrip G4

BCP380 24LEDLP 30K 24V A4 L51 DMX

UniStrip G4, 370 lm, 5.6 W, Warm white, 25° x 40°, Dynamix DMX, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Color rendering index (CRI)	
Light source replaceable	No	Light source color	Warm white
Driver included	No	Optical cover type	Clear flat
Light source engine type	LED	Luminaire light beam spread	25° x 40°
Lighting Technology	LED	Operating and Electrical	
CE mark	CE mark	Input Voltage	24 DC V
Flammability mark	For mounting on normally flammable surfaces	Line Frequency	- Hz
Light Technical		Power Consumption	5.6 W
Luminous Flux	370 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	3000 K	Connection	2 Push-in connector 5-pole
Luminous Efficacy (rated) (Nom)	66 lm/W		

UniStrip G4

Cable	2 cables 0.15m with connectors 5-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamix DMX
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	510 mm
Overall width	35 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 35 x 510 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%
Product Data	
Order product name	BCP380 24LEDLP 30K 24V A4 L51 DMX
Full product name	BCP380 24LEDLP 30K 24V A4 L51 DMX
Full product code	911401738332
Order code	911401738332
Material Nr. (12NC)	911401738332
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30

Dimensional drawing

