

UniStrip G4

BCP381 24LED 40K 24V 40 L100 DMX

UniStrip G4, 1748 lm, 24 W, Neutral white, 40° x 40°, Dynamix DMX, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces

Light Technical	
Luminous Flux	1,748 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color rendering index (CRI)	80
Light source color	Neutral white
Optical cover type	Clear flat
Luminaire light beam spread	40° x 40°

Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	24 W
Power Factor (Fraction)	0.9
Connection	2 Push-in connector 5-pole

UniStrip G4

Cable	2 cables 0.15m with connectors 5-pole

Temperature

Ambient temperature range	-40 to +50 °C

Controls and Dimming

Dimmable	Yes
Control interface	Dynamix DMX

Mechanical and Housing

Housing Material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	1,000 mm
Overall width	38 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 38 x 1000 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP381 24LED 40K 24V 40 L100 DMX
Full product name	BCP381 24LED 40K 24V 40 L100 DMX
Full product code	871951494460299
Order code	911401738872
Material Nr. (12NC)	911401738872
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514944602
Numerator - Packs per outer box	15
EAN/UPC - Case	8719514944602

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.