

# UniStrip G4

## BCP382 12LED RGBNW 24V A4 L50 DMX

UniStrip G4 is a surface-mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications.;One family that fits all your needs, wall washing, grazing and also linear flood lighting.;The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution.;Available in white, monochromatic colours, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Product data

General Information	
Light source colour	Red, green, blue and white (RGBW)
Light source replaceable	No
Driver included	No
Optical cover/lens type	CLFT [ Clear flat]
Luminaire light beam spread	25° x 40°
Control interface	Dynamix DMX
Connection	2 push-in connectors 5-pole
Cable	2 cables 0.15 m with connectors 5-pole
Protection class IEC	Safety class III (III)
Flammability mark	F [ For mounting on normally flammable surfaces]
CE mark	CE mark
LED engine type	LED
Operating and Electrical	
Input voltage	24 DC V
Input frequency	- Hz
Power factor (min.)	0.9

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover/lens material	Tempered glass
Fixation material	Aluminum
Mounting device	MBA [ Mounting bracket adjustable]
Optical cover/lens finish	Clear
Overall length	500 mm
Overall width	38 mm
Overall height	47 mm
Colour	Dark gray
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [ 1 J]

# UniStrip G4

## Initial Performance (IEC Compliant)

Initial luminous flux	579 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	32 lm/W
Init. colour rendering index	-
Initial input power	18 W
Power consumption tolerance	+/-10%

## Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


## Product Data

Full product code	911401739102
Order product name	BCP382 12LED RGBNW 24V A4 L50 DMX
Order code	01739102
Numerator – quantity per pack	1
Numerator – packs per outer box	15
Material no. (12NC)	911401739102
Net weight (piece)	0.899 kg



## Warnings and Safety

## Dimensional drawing



BCP280/383/384/385 UNiStrip G3

