



UniStrip G4

BCP382 36LED 40K 24V 40 L100

UniStrip G4, 2557 lm, 36 W, Neutral white, 40° x 40°, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

| General Information | | Color rendering index (CRI) | |
|------------------------------------|---|-----------------------------|----------------------------|
| Light source replaceable | No | Light source color | Neutral white |
| Driver included | No | Optical cover type | Clear flat |
| Light source engine type | LED | Luminaire light beam spread | 40° x 40° |
| Lighting Technology | LED | Operating and Electrical | |
| CE mark | CE mark | Input Voltage | 24 DC V |
| Flammability mark | For mounting on normally flammable surfaces | Line Frequency | - Hz |
| Light Technical | | Power Consumption | 36 W |
| Luminous Flux | 2,557 lm | Power Factor (Fraction) | 1 |
| Correlated Color Temperature (Nom) | 4000 K | Connection | 2 Push-in connector 2-pole |
| Luminous Efficacy (rated) (Nom) | 71 lm/W | | |

UniStrip G4

| | |
|-------------------------------------|---------------------------------------|
| Cable | 2 cables 0.15m with connectors 2-pole |
| Temperature | |
| Ambient temperature range | -40 to +50 °C |
| Controls and Dimming | |
| Dimmable | No |
| Control interface | - |
| Mechanical and Housing | |
| Housing Material | Aluminum extruded |
| Optic material | Polymethyl methacrylate |
| Optical cover material | Tempered glass |
| Fixation material | Aluminum |
| Housing Color | Dark gray |
| Mounting device | Mounting bracket adjustable |
| Optical cover finish | Clear |
| Overall length | 1,000 mm |
| Overall width | 38 mm |
| Overall height | 47 mm |
| Dimensions (Height x Width x Depth) | 47 x 38 x 1000 mm |

| | |
|--|--|
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |
| Protection class IEC | Safety class III |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | 4 SDCM |
| Power consumption tolerance | +/-10% |
| Product Data | |
| Order product name | BCP382 36LED 40K 24V 40 L100 |
| Full product name | BCP382 36LED 40K 24V 40 L100 |
| Full product code | 872016972711399 |
| Order code | 911401739502 |
| Material Nr. (12NC) | 911401739502 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169727113 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8720169727113 |

Dimensional drawing

