



UniStrip G4

BCP382 9LED 27K 24V 40 L30

UniStrip G4, 619 lm, 9 W, Warm white, 40° x 40°, Safety class III, Mounting bracket adjustable

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Color rendering index (CRI)	
Light source replaceable	No	Color rendering index (CRI)	80
Driver included	No	Light source color	Warm white
Light source engine type	LED	Optical cover type	Clear flat
Lighting Technology	LED	Luminaire light beam spread	40° x 40°
CE mark	CE mark	Operating and Electrical	
Flammability mark	For mounting on normally flammable surfaces	Input Voltage	24 DC V
Light Technical		Line Frequency	- Hz
Luminous Flux	619 lm	Power Consumption	9 W
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	1
Luminous Efficacy (rated) (Nom)	69 lm/W	Connection	2 Push-in connector 2-pole

UniStrip G4

Cable	2 cables 0.15m with connectors 2-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	300 mm
Overall width	38 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 38 x 300 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data	
Order product name	BCP382 9LED 27K 24V 40 L30
Full product name	BCP382 9LED 27K 24V 40 L30
Full product code	872016972568399
Order code	911401739602
Material Nr. (12NC)	911401739602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169725683
Numerator - Packs per outer box	30
EAN/UPC - Case	8720169725683

Dimensional drawing

