



UniEdge

BCP390 3LED RGB 24V 3x90 DMX

UniEdge, 67 lm, 7 W, Red, green and blue, 3° x 90°, Dynamix DMX, Safety class III, Mounting bracket adjustable

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	67 lm
Standard tilt angle posttop	-
Correlated Color Temperature (Nom)	-

Luminous Efficacy (rated) (Nom)	6.7 lm/W
Color rendering index (CRI)	-
Light source color	Red, green and blue
Optical cover type	Clear flat
Luminaire light beam spread	3° x 90°
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	7 W
Power Factor (Fraction)	0.9
Connection	2 Push-in connector 5-pole

Cable	2 cables 0.3m with connector 5-pole
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamix DMX
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	181 mm
Overall width	51 mm
Overall height	58 mm
Dimensions (Height x Width x Depth)	58 x 51 x 181 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	-
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	13%
Product Data	
Order product name	BCP390 3LED RGB 24V 3x90 DMX
Full product name	BCP390 3LED RGB 24V 3x90 DMX
Full product code	911401739742
Order code	911401739742
Material Nr. (12NC)	911401739742
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

Dimensional drawing

