



# UniEdge

## BCP390 4LED 30K 24V 3x90

UniEdge, 127 lm, 10 W, Warm white, 3° x 90°, Safety class III,  
Mounting bracket adjustable

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	127 lm
Standard tilt angle posttop	-
Correlated Color Temperature (Nom)	3000 K

Luminous Efficacy (rated) (Nom)	12.7 lm/W
Color rendering index (CRI)	80
Light source color	Warm white
Optical cover type	Clear flat
Luminaire light beam spread	3° x 90°
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	10 W
Power Factor (Fraction)	0.9
Connection	2 Push-in connector 2-pole

Cable	2 cables 0.3m with connector 2-pole
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	No
Control interface	-
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	181 mm
Overall width	51 mm
Overall height	58 mm
Dimensions (Height x Width x Depth)	58 x 51 x 181 mm

<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class III
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM = 4
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BCP390 4LED 30K 24V 3x90
Full product name	BCP390 4LED 30K 24V 3x90
Full product code	911401739772
Order code	911401739772
Material Nr. (12NC)	911401739772
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

## Dimensional drawing

