



Uni DMX controls and accessories

ZXP399 main controller DMX/RDM

Uni DMX controls and accessories, 90 to 264 V, 50 to 60 Hz, Finger-protected, CE mark, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include a main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6,000 DMX universes. Stand-alone Controller: Fits all medium applications with up to 700 DMX universes. Wiring accessories include leader and jump cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low-power repeater that can amplify the DMX signal for up 100 metres.

Product data

General Information		Overall height		177 mm
Accessory color	Black	Dimensions (Height x Width x Depth)		177 x 361 x 482 mm
CE mark	CE mark			
Operating and Electrical		Approval and Application		
Input Voltage	90 to 264 V	Ingress protection code		IP20 [Finger-protected]
Line Frequency	50 to 60 Hz			
Mechanical and Housing		Product Data		
Overall length	482 mm	Order product name		ZXP399 main controller DMX/RDM
Overall width	361 mm	Full product name		ZXP399 main controller DMX/RDM
		Full product code		871951494686600
		Order code		911401756622

Uni DMX controls and accessories

Material Nr. (12NC)	911401756622
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946866
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514946866
----------------	---------------

Dimensional drawing

