



# Uni DMX controls and accessories

## ZXP399 sub-controller 12V 8 port DMX/RDM

Uni DMX controls and accessories, 12 DC V, Finger-protected, CE mark, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

### Product data

General Information	
Accessory color	Black
CE mark	CE mark
Operating and Electrical	
Input Voltage	12 DC V
Line Frequency	– Hz
Mechanical and Housing	
Overall length	277.6 mm
Overall width	193 mm

Overall height	66 mm
Dimensions (Height x Width x Depth)	66 x 193 x 278 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	ZXP399 sub-controller 12V 8 port DMX/RDM
Full product name	ZXP399 sub-controller 12V 8 port DMX/RDM
Full product code	871951494691099
Order code	911401756672

Uni DMX controls and accessories

Material Nr. (12NC)	911401756672
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946910
Numerator - Packs per outer box	2

EAN/UPC - Case	8719514946910
----------------	---------------

Dimensional drawing

