



ZXP399 DMX Controls and Accessories

ZXP399 DMX amplifier 24V 4P

12 to 24 DC V - - Hz - Dust penetration-protected, jet-proof - CE mark

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar).;DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device.;Main Controller: Industrial computer that can control up to 6000 DMX universes.;Stand-alone Controller: Fits for medium applications with up to 700 DMX universes.;Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps.;Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes.;DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

Product data

General Information	
CE mark	CE mark
Accessory color	Black
Operating and Electrical	
Input Voltage	12 to 24 DC V

Input Frequency	- Hz
Mechanical and Housing	
Overall length	136.4 mm
Overall width	40 mm
Overall height	25.2 mm


ZXP399 DMX Controls and Accessories

Dimensions (Height x Width x Depth)	25 x 40 x 136 mm (1 x 1.6 x 5.4 in)
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Full product code	911401756682
Order product name	ZXP399 DMX amplifier 24V 4P

Order code	911401756682
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	911401756682
Net Weight (Piece)	0.149 kg

IP65

Dimensional drawing



ZXP399

