



Uni DMX controls and accessories

ZXP399 DMX amplifier 24V 4P

Uni DMX controls and accessories, 12 to 24 DC V, Dust penetration-protected, jet-proof, CE mark, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

Product data

General Information	
Accessory color	Black
CE mark	CE mark
Operating and Electrical	
Input Voltage	12 to 24 DC V
Line Frequency	- Hz
Mechanical and Housing	
Overall length	136.4 mm
Overall width	40 mm

Overall height	25.2 mm
Dimensions (Height x Width x Depth)	25 x 40 x 136 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	ZXP399 DMX amplifier 24V 4P
Full product name	ZXP399 DMX amplifier 24V 4P
Full product code	871951494692799
Order code	911401756682

Uni DMX controls and accessories

Material Nr. (12NC)	911401756682
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946927
Numerator - Packs per outer box	12

EAN/UPC - Case	8719514946927
----------------	---------------

Dimensional drawing

