



Uni DMX controls and accessories

ZXP399 DMX/RDM amplifier 24V 4P

Uni DMX controls and accessories, 12 to 24 DC V, Dust penetration-protected, jet-proof, CE mark, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up to 100 meters.

Product data

General Information		Overall height	
Accessory color	Black		25.2 mm
CE mark	CE mark	Dimensions (Height x Width x Depth)	
			25 x 40 x 136 mm
Operating and Electrical		Approval and Application	
Input Voltage	12 to 24 DC V	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Line Frequency	- Hz	Product Data	
Mechanical and Housing		Order product name	ZXP399 DMX/RDM amplifier 24V 4P
Overall length	136.4 mm	Full product name	ZXP399 DMX/RDM amplifier 24V 4P
Overall width	40 mm	Full product code	871951494694199
		Order code	911401756702

Uni DMX controls and accessories

Material Nr. (12NC)	911401756702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946941
Numerator - Packs per outer box	12

EAN/UPC - Case	8719514946941
----------------	---------------

Dimensional drawing

