



# ZXP399 DMX Controls and Accessories

## ZXP399 DMX/RDM amplifier 24V 5P

12 to 24 DC V - - Hz - Dust penetration-protected, jet-proof - CE mark

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar).;DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device.;Main Controller: Industrial computer that can control up to 6000 DMX universes.;Stand-alone Controller: Fits for medium applications with up to 700 DMX universes.;Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps.;Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes.;DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

### Product data

General Information	
CE mark	CE mark
Accessory color	Black
Operating and Electrical	
Input Voltage	12 to 24 DC V

Input Frequency	- Hz
Mechanical and Housing	
Overall length	136.4 mm
Overall width	40 mm
Overall height	25.2 mm


## ZXP399 DMX Controls and Accessories

<b>Dimensions (Height x Width x Depth)</b>	25 x 40 x 136 mm (1 x 1.6 x 5.4 in)
<b>Approval and Application</b>	
<b>Ingress protection code</b>	IP65 [ Dust penetration-protected, jet-proof]
<b>Product Data</b>	
<b>Full product code</b>	911401756712
<b>Order product name</b>	ZXP399 DMX/RDM amplifier 24V 5P

<b>Order code</b>	911401756712
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	12
<b>Material Nr. (12NC)</b>	911401756712
<b>Net Weight (Piece)</b>	0.157 kg

IP65

### Dimensional drawing



ZXP399

