



UrbanSpark

BDP301 LED 6M 7043

Integrated solar post top lantern with Lithium Ferro Phosphate battery, vertically mounted mono-crystalline solar panel and MPPT charger. Extruded aluminium construction for sturdiness and long life. Choice of street light and post top optics and pole height of 4 & 6 meters. Charger and battery accommodated inside the pole and accessible through service hatch for ease of maintenance. Vertically mounted panels on all four sides to catch sunlight throughout the day. IP-68 battery to prevent damage in case of water logging.

Product data

Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	18 Vmp, 23 Voc V
Panel peak wattage	360 W

Mechanical and Housing	
Housing Material	Aluminum Alloy
Overall length	172 mm
Overall width	172 mm
Overall height	4000 mm
Color	RAL 7043

Application Conditions	
Ambient temperature range	+32 to +95 °F

Product Data	
Order product name	BDP301 LED 6M 7043
Order code	911401800502
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401800502
Net Weight (Piece)	88.000 kg