



Smartbright CCT/ Wattage Tunable Waterproof batten

WT067C SWT SCCT LED L1200 PSU AU

Smartbright CCT/Wattage Tunable Waterproof batten, 40 W, 4000 lm, 120°

The new SmartBright Tri Colour Waterproof Batten provides flexibility the customer to choose from 3 colour temperatures and 2 wattages before installation, to suit specific needs.

Product data

| General Information | |
|------------------------------------|-----------------------------------|
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver included | Yes |
| Light source engine type | LED |
| CE mark | - |
| Warranty period | 5 years |
| Flammability mark | - |
| ENEC mark | - |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| EU RoHS compliant | No |
| Light Technical | |
| Luminous Flux | 4,000 lm |
| Correlated Color Temperature (Nom) | - |


| Luminous Efficacy (rated) (Nom) | 100 lm/W |
|---------------------------------|--------------------------|
| Color rendering index (CRI) | >80 |
| Beam angle of light source | 120 degree(s) |
| Light source color | White |
| Optic type | Beam angle 120° |
| Optical cover type | Polycarbonate bowl/cover |
| Luminaire light beam spread | 120° |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Inrush current | 12.8 A |
| Inrush time | 0.04 ms |
| Power Consumption | 40 W |
| Power Factor (Fraction) | 0.9 |

Smartbright CCT/Wattage Tunable Waterproof batten

| | |
|--|--|
| Connection | Connection unit 3-pole |
| Cable | - |
| Number of products on MCB of 16 A type B | 26 |
| Temperature | |
| Ambient temperature range | -20 to +40 °C |
| Controls and Dimming | |
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |
| Mechanical and Housing | |
| Housing Material | Polycarbonate |
| Reflector material | Steel |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | - |
| Housing Color | Grey |
| Optical cover finish | Opal |
| Overall length | 1,265 mm |
| Overall width | 107 mm |
| Overall height | 72 mm |
| Dimensions (Height x Width x Depth) | 72 x 107 x 1265 mm |
| Approval and Application | |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Protection class IEC | Safety class I |

| | |
|---------------------------------------|----------------------------------|
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | 0.38;0.38 |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Driver failure rate at 5000 h | 0.003 % |
| Median useful life L70B50 | 72,000 h |
| Median useful life L80B50 | 44,000 h |
| Median useful life L90B50 | 21,000 h |
| Application Conditions | |
| Maximum dim level | Not applicable |
| Product Data | |
| Order product name | WT067C SWT SCCT LED L1200 PSU AU |
| Full product name | WT067C SWT SCCT LED L1200 PSU AU |
| Full product code | 871016334431799 |
| Local code description | WT067CSWTL1200P |
| Order code | 911401821780 |
| Material Nr. (12NC) | 911401821780 |
| Local order code | WT067CSWTL1200P |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163344317 |
| Numerator - Packs per outer box | 9 |
| EAN/UPC - Case | 8710163344331 |

Dimensional drawing



Smartbright CCT/Wattage Tunable Waterproof batten

