



Smartbright CCT/ Wattage Tunable Waterproof batten

WT067C SWT SCCT LED L1200 PSU AU

Power supply unit - Beam angle 120° - Polycarbonate bowl/
cover - 120°

The new SmartBright Tri Colour Waterproof Batten provides flexibility the customer to choose from 3 colour temperatures and 2 wattages before installation, to suit specific needs.

Product data

General Information		Operating and Electrical	
Beam angle of light source	120 °	Flammability mark	NO [-]
Lamp colour code	White	CE mark	-
Light source replaceable	No	ENEC mark	-
Number of gear units	1 unit	Warranty period	5 years
Driver/power unit/transformer	PSU [Power supply unit]	Constant light output	No
Driver included	Yes	Number of products on MCB	26
Optic type	120 [Beam angle 120°]	LED engine type	LED
Optical cover/lens type	PC [Polycarbonate bowl/cover]		
Luminaire light beam spread	120°	Input voltage	220 to 240 V
Control interface	-	Input frequency	50 or 60 Hz
Connection	CU3 [Connection unit 3-pole]	Inrush current	12.8 A
Cable	-	Inrush time	0.04 ms
Protection class IEC	Safety class I (I)	Power factor (min.)	0.9
Glow-wire test	650/30 [Temperature 650 °C., duration 30 s]		

Smartbright CCT/Wattage Tunable Waterproof batten

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Opal
Overall length	1265 mm
Overall width	107 mm
Overall height	72 mm
Colour	Grey

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Lamp colour temperature	- K
Colour Rendering Index	>80

Initial chromaticity	0.38;0.38
Initial input power	40 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	72000 h
Median useful life L80B50	44000 h
Median useful life L90B50	21000 h

Application Conditions


Ambient temperature range	-20 to +40 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871016334431799
Order product name	WT067C SWT SCCT LED L1200 PSU AU
EAN/UPC – product	8710163344317
Order code	911401821780
Numerator – quantity per pack	1
Numerator – packs per outer box	9
Material no. (12NC)	911401821780
Net weight (piece)	1.800 kg



Dimensional drawing



WT066C/WT067C

Smartbright CCT/Wattage Tunable Waterproof batten

