



Greenperform Waterproof G2 - WT188C

WT188C LED40 NW L1200 PSU TB

Greenperform Waterproof G2 - WT188C, 34 W, 4000 lm, 4000 K, 120°

Greenperform Waterproof G2 luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser, stainless steel installation accessory). We design for friendly optical, energy saving, reliable quality, and easy wiring. Beyond that, GreenParking wireless motion detective system is ready to provide the maximum energy saving and new lighting experience to you.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	4,000 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	117 lm/W
Light source engine type	LED	Color rendering index (CRI)	>80
CE mark	CE mark	Beam angle of light source	- degree(s)
Warranty period	3 years	Light source color	Neutral white
Flammability mark	-	Optic type	Symmetrical
ENEC mark	-	Optical cover type	Polycarbonate bowl/cover foggy
Glow-wire test	Temperature 750 °C, duration 5 s	Luminaire light beam spread	120°
EU RoHS compliant	Yes		

Greenperform Waterproof G2 - WT188C

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	12 A
Inrush time	0.59 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Screw connection block
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Optical cover finish	Opal
Overall length	1,183 mm
Overall width	84 mm
Overall height	83 mm
Dimensions (Height x Width x Depth)	83 x 84 x 1183 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 h
Median useful life L80B50	45,000 h
Median useful life L90B50	35,000 h


Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	WT188C LED40 NW L1200 PSU TB
Full product name	WT188C LED40 NW L1200 PSU TB
Full product code	872016954956200
Order code	911401830697
Material Nr. (12NC)	911401830697
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169549562
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169549562

Dimensional drawing



Greenperform Waterproof G2 - WT188C

