



UNIstrip LP G2

BCP270 G2 72xLED/RGB 24V L1200 A DMX RU

UNIstrip LP Gen2 is an evolution in both optical and system design. It offers Mono and RGB DMX versions with precision optical performance to enable dynamic effects with affordable pricing.

Product data

General Information	
Light source color	Red, green and blue
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	Electronic transformer
Driver included	No
Optical cover/lens type	Polycarbonate linear
Control interface	Dynamix DMX
Connection	Flying leads/wires
Cable	Cable 1.0 m without plug
Protection class IEC	Safety class III
Flammability mark	For mounting on normally flammable surfaces
CE mark	-
ENEC mark	-
Warranty period	3 years
Constant light output	No
EU RoHS compliant	Yes
Light source engine type	LED
Light Technical	
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Operating and Electrical	
Input Voltage	24 DC V
Power Factor (Min)	0.9
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	1216 mm
Overall width	50 mm
Overall height	61 mm
Color	Aluminum and black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK03 [0.3 J]

UNIStrip LP G2

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	480 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	32 lm/W
Init. Corr. Color Temperature	- K
Init. Color Rendering Index	-
Initial input power	14.8 W
Power consumption tolerance	+/-10%

Application Conditions


Ambient temperature range	-40 to +50 °C
Maximum dim level	0% (digital)

Product Data

Full product code	911401856698
Order product name	BCP270 G2 72xLED/RGB 24V L1200 A DMX RU
Order code	911401856698
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	911401856698
Net Weight (Piece)	1.049 kg



Dimensional drawing



BCP270 UNIStrip LP G2

