



# SmartBright All-in-one Solar Street Light

## BRP110 LED50/757

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Independently tilt-able LED source and pole mounting bracket allows light beam to focus on road, and solar panel towards the sun. Microwave based motion sensor for optimizing battery autonomy.

### Product data

General Information	
Driver included	Yes
Warranty period	2 years
Light Technical	
Luminous Flux	5,000 lm
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Optical cover type	Polycarbonate
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	24 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	18 V
Panel peak wattage	50 W
Charge controller type	MPPT

Charge controller wattage	35 W
Temperature	
Ambient temperature range	-20 to +50 °C
Controls and Dimming	
Dimmable	Yes
Configurability	Configurable
Control interface	IR remote
Mechanical and Housing	
Overall length	935 mm
Overall width	380 mm
Overall height	95 mm
Dimensions (Height x Width x Depth)	95 x 380 x 935 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

# SmartBright All-in-one Solar Street Light

Mech. impact protection code	IK08 [5 J vandal-protected]
<b>Application Conditions</b>	
Ambient temperature range for charging	0 °C to +45 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +50 °C
Autonomy	up to 24 hour(s)
Solar dimming profile	First 2 Hrs - On motion : 100%, without motion :30% ; Next 3 Hrs - On motion : 60%, without motion :20% ; Next 6 Hrs On motion : 30%, without motion :10% ; Rest of the Night: On motion : 50%, without motion :30%
Grid connection type	Off grid
Battery location	Inside Luminaire

<b>Product Data</b>	
Order product name	BRP110 LED50/757
Full product name	BRP110 LED50/757
Full product code	871951450821700
Order code	911401863681
Material Nr. (12NC)	911401863681
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514508217
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514508217

## Dimensional drawing

