



Smartbright Waterproof G3 WT068C

WT068C CW LED36 L1200 PSU

Smartbright Waterproof G3 WT068C, 33 W, 3600 lm, 6500 K

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Product data

General Information	
Light source engine type	LED
CE mark	CE mark
Light Technical	
Luminous Flux	3,600 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	33 W

Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 1	
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White and gray
Optical cover finish	Opal
Overall length	1,188 mm

Smartbright Waterproof G3 WT068C

Overall width	69 mm
Overall height	74 mm
Dimensions (Height x Width x Depth)	74 x 69 x 1188 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	WT068C CW LED36 L1200 PSU
Full product name	WT068C CW LED36 L1200 PSU
Full product code	871016336060799
Order code	911401881480
Material Nr. (12NC)	911401881480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163360607
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163360720

Dimensional drawing

WT068C-4ft

