



Smartbright Waterproof G3 WT068C

WT068C NW LED56 L1500 PSU

Smartbright Waterproof G3 WT068C, 51 W, 5600 lm, 4000 K

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Product data

General Information		Power Factor (Fraction) 0.9	
Light source engine type	LED	Number of products on MCB of 16 A type B 1	
CE mark	CE mark		
Light Technical		Temperature	
Luminous Flux	5,600 lm	Ambient temperature range -20 to +45 °C	
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	110 lm/W	Dimmable No	
Color rendering index (CRI)	>80	Control interface -	
Light source color	840 neutral white	Mechanical and Housing	
Optical cover type	-	Housing Material Polycarbonate	
Operating and Electrical		Optical cover material Polycarbonate	
Input Voltage	220 to 240 V	Housing Color White and gray	
Line Frequency	50 or 60 Hz	Optical cover finish Opal	
Power Consumption	51 W	Overall length 1,488 mm	

Smartbright Waterproof G3 WT068C

Overall width	69 mm
Overall height	74 mm
Dimensions (Height x Width x Depth)	74 x 69 x 1488 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	WT068C NW LED56 L1500 PSU
Full product name	WT068C NW LED56 L1500 PSU
Full product code	871016336064599
Order code	911401881880
Material Nr. (12NC)	911401881880
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163360645
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163360768

Dimensional drawing

WT068C-5ft

