



CoreLine recessed

RC132Z SMB-PLC

CoreLine recessed, Accessory, Nickel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Product data

General Information	
Angle	-
Accessory colour	Nickel
Value ladder	Performance

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz

Mechanical and Housing	
Overall length	55 mm
Overall width	25 mm

Overall height	30 mm
Dimensions (height x width x depth)	30 x 25 x 55 mm
Material	Steel

Approval and Application	
Protection class IEC	-

Product Data	
Order product name	RC132Z SMB-PLC
Full product name	RC132Z SMB-PLC
Full EOC	871016336269499
Order code	36269499

CoreLine recessed

Material no. (12 NC)	911401892180
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163362694
Numerator – packs per outer box	10

EAN/UPC - Case	8710163362762
----------------	---------------

